

General Tolerance except Pre-stretched film.

Internal Ø (mm)	Core length (mm)	Core weight (g)	Film Thickness (µ)	Film width (mm) ^a	Film length	Core weight	Internal Core Ø (mm)	Core length (mm)	Reel weight
50	520	200/300	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±7%	±1,5	+6 -3	±5%
50	520	500	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±10%	±1,5	+6 -3	±5%
50	520	600/700/800	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±9%/±8%/±7%	±1,5	+6 -3	±5%
50	470	180/270/450	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	± 7%	±1,5	+6 -3	±5%
50	260	220	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±7%	±1,5	+6 -3	±5%
50	153/128/103	267/224/180	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±3	±5%	±7%	±1,5	+6 -3	±5%
38	140/128/103	85/75/60	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±3	±5%	±8%	±1,5	+3 -2	±5%
38 R ^b	103/128/260	89/110/220	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±3	±5%	±7%	±1,5	+3 -2	±5%
76	520 ^c	850	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±5%	±1,5	+6 -3	±5%
76	510/510/1010	1.000/1.700/3.367	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±5%	±1,5	+6 -3	±5%
76	385/510/760	1.283/1.800/2.550	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±5%	±1,5	+6 -3	±5%
76 ^d	510	1.860	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±5%	±1,5	+6 -3	±5%
76	510	1.950	23-35 ±2	±8	±5%	±7%	±1,5	+6 -3	±5%
76	255/128/103	850/427/333	7-23 ±1 - 24-35 ±2 – 36-80 ±3	±8	±5%	±5%	±1,5	+6 -3	±5%

^a During the first 20 meters of the coil ±25 mm. In case of reinforced edges the value of 8 mm will be of 15 mm

^b Reinforced core.

^c To be used only in 5Kg total reel weight.

^d Plastic core. To be used only for printed Films. Non-returnable plastic core.

The above values are to be considered as indicative in order to facilitate the choice and usage, but are not given for guarantee purposes. Hipac Group reserves the right to modify them, if necessary, without previous notice. The present document is property of Hipac S.p.A. It cannot be copied, published or redistributed without prior written consent of Hipac S.p.A.

HIPAC SpA: Via per Rovato, 10 25046 Cazzago S. Martino (Brescia) – ITALY Phone: +39 030 7750610 Fax:+39 030 7750847.

IBERHIPAC SA: Crta N-V Km 189,1 10390 Saucedilla (Cáceres) - SPAIN Phone: +34 927 545188 Fax:+34 927 545187.

HIPAC ROMANIA srl: Dragomiresti Vale, Ilfov (Bucuresti) – ROMANIA Phone: +40 21 3523600 Fax:+40 21 3523608.

Visit us at www.hipac.it

TECHNICAL SPECIFICATIONS



17/5/2021 rel.27

Pre-stretched film Tolerance.

Internal Ø (mm)	Core length	Film Average Thickness (µ)	Film width (mm)	Film length	Core weight	Internal Core Ø (mm)	Core length (mm)	Reel weight
76	460 mm weight 1,533 Kg	±1	±10	±7%	±5%	±1,5	+6 -3	± 7%
50	470 mm weight 0,27 Kg	±1	±10	±7%	±7%	±1,5	+6 -3	± 7%
50	470 mm weight 0,45 Kg	±1	±10	±7%	±7%	±1,5	+6 -3	± 7%

“Sunlight Resistance” for the printing on printed film.

June-July-August	September-April-May	October-November-March	December-January-February
40 days	120 days	240 days	720 days

- The above mentioned values (tested with instrument XENOTEST 150 S) are considered with the sunlight in the range of the Washington meridian; Exposure from 9:00 to 15:00.
- Although HIPAC uses colours with “Light Resistance” index 7 for printing but due to the fact that the film can be exposed under innumerable situations which mean uncontrolled solar radiation quantities absorbed, HIPAC does not guarantee the duration and appearance of the printing in printed films.

Printed film Tolerance.

For printed films the printing width and/or height can vary, depending on the thickness, by 5%.

The above values are to be considered as indicative in order to facilitate the choice and usage, but are not given for guarantee purposes. Hipac Group reserves the right to modify them, if necessary, without previous notice. The present document is property of Hipac S.p.A. It cannot be copied, published or redistributed without prior written consent of Hipac S.p.A.

HIPAC SpA: Via per Rovato, 10 25046 Cazzago S. Martino (Brescia) – **ITALY** Phone: +39 030 7750610 Fax:+39 030 7750847.

IBERHIPAC SA: Crta N-V Km 189,1 10390 Saucedilla (Cáceres) - **SPAIN** Phone: +34 927 545188 Fax:+34 927 545187.

HIPAC ROMANIA srl: Dragomiresti Vale, Ilfov (Bucuresti) – **ROMANIA** Phone: +40 21 3523600 Fax:+40 21 3523608.

Visit us at www.hipac.it

TECHNICAL SPECIFICATIONS



17/5/2021 rel.27

NETROLL Film tolerances

Roll type	Film Thickness (μ)	Film width (mm) ⁱ	Film length	Roll Type	Internal Core \varnothing (mm) *	Reel weight
Automatic	9-23 \pm 1 - 24-35 \pm 2	\pm 8	\pm 5%	Automatic	74 \pm 4	\pm 5%
Manual	9-23 \pm 1 - 24-35 \pm 2	\pm 8	\pm 5%	Manual	45 \pm 5	\pm 5%

* This value is considered as indicative.
Hipac has an official dispenser that grants the use of the roll in terms of inner diameter.
Hipac does not give warranty on another dispenser.

ⁱ During the first 20 meters of the coil \pm 25 mm. In case of reinforced edges the value of 8 mm will be of 15 mm

The above values are to be considered as indicative in order to facilitate the choice and usage, but are not given for guarantee purposes. Hipac Group reserves the right to modify them, if necessary, without previous notice. The present document is property of Hipac S.p.A. It cannot be copied, published or redistributed without prior written consent of Hipac S.p.A.

HIPAC SpA: Via per Rovato, 10 25046 Cazzago S. Martino (Brescia) – **ITALY** Phone: +39 030 7750610 Fax:+39 030 7750847.
IBERHIPAC SA: Crta N-V Km 189,1 10390 Saucedilla (Cáceres) - **SPAIN** Phone: +34 927 545188 Fax:+34 927 545187.
HIPAC ROMANIA srl: Dragomiresti Vale, Ilfov (Bucuresti) – **ROMANIA** Phone: +40 21 3523600 Fax:+40 21 3523608.

Visit us at www.hipac.it